



Straight Blade Receptacles, Decorator Duplex, Commercial, Corrosion Resistant, 15A 125V, 2- Pole 3-Wire Grounding, 5-15R, Back and Side Wired, White

By Hubbell Wiring Device-Kellems
Catalog # [IG15DRW](#)



Straight Blade Devices, Receptacles, Decorator Duplex,
Commercial Grade, Corrosion Resistant, 15A 125V, 2- Pole 3-
Wire Grounding, 5-15R, Back and Side Wired, White

Features

- Triangle marking on face indicates isolated ground
- Aesthetic Style Line® decorator design
- Triple wipe contacts

Application

Heavy Duty

General

Color	<ul style="list-style-type: none">• White• Blanc
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Isolated Ground
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device- Kellems
UPC	783585146867

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 VAC
Wattage	1875

Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG

Certifications and Compliance

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Engineering Drawing - IG15DRW AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1579_PD2305_INSTALLINST](#)
[Sales Drawings - WDK_IG15DRW_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)

Related Products

[IG5261 - Straight Blade Devices, Isolated Ground, Receptacles, Single, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Single Pack](#)

[IG8210 - Straight Blade Devices, Receptacles, Single, Isolated Ground, Hospital Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Orange, Single Pack](#)

[IG2182I - Straight Blade Devices, Receptacles, Duplex, Hospital/Decorator Grade, Isolated Ground, 2-Pole 3-Wire Grounding, 20A 125V, 5- 20R, Ivory, Single Pack.](#)

[IG9308 - Straight Blade Devices, Receptacles, Flush Receptacle, Industrial Grade, 2-Pole 3-Wire Grounding, 30A 125V, 5-30R, Orange, Single Pack](#)

[IG5262 - Straight Blade Devices, Receptacles, Duplex, Industrial Grade, Isolated ground, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Orange, Single Pack](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-IG15DRW-SPEC-EN | REV 5/2023

