



IG TVSS Duplex Receptacle with Light and Alarm, 15A 125V, 5-15R, Office White

By Hubbell Wiring Device-Kellems
 Catalog # [IG5262OWSA](#)



IG TVSS Duplex Receptacle with Light and Alarm, 15A 125V, 5-15R, Office White

Application

Decorator Duplex with Light and Alarm

General

Color	Office White
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED and Audible Alarm
Item Type	Surge Protection Receptacles
Material	Composite
Material - Mounting Hardware	Mounting Screws
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade
Performance	<ul style="list-style-type: none"> • Electrical - Protection Modes - Normal and Common Modes • Electrical - Response Time - Approximately 5 ns • Electrical - Transient Suppression - Peak Energy (10 X 100 μs), Peak Current (8 X 20 μs) • Electrical - Voltage - 120V AC + 10% - 15% • Environmental - Flammability - UL 94V-2 • Environmental - Operating Temperature - 32°F to 140°F (0°C to 60°C)
Response Time	5
Series	Specification Grade
Style	Isolated Ground
Type	Duplex
UPC	783585060651

Dimensions

Display Size	Standard
--------------	----------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Terminal Screws
Current / Amperage Rating	15 A
Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • CSA Certified to Specification C22.2 No. 42 • Listed to UL Standards 498 • UL Listed File E2186
----------------------	---

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - Wiring N-13 Catalog page](#)
- [Catalogs - Wiring Full Catalog](#)
- [Engineering Drawing - IG5262OWSA AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD1152_INSTALLINST](#)
- [Literature - SpikeShield® Power Quality Surge Protective Devices](#)
- [Sales Drawings - WDK_IG5262_DRAWING_PDF](#)
- [Warranty - Industrial & Commercial Products](#)

Related Products

- [HBL5260OWSA - Surge Protective Devices, SPIKESHIELD TVSS Duplex Receptacle with Light, 15A 125V, 5-15R, Office White](#)
- [HBL5262OWSA - TVSS Duplex Receptacle with Light and Alarm, 15A 125V, 5-15R, Gray](#)
- [SS8 - Wallplates and Boxes, Metallic Plates, 1- Gang, 1\) Duplex Opening, Standard Size, Stainless Steel](#)
- [IG5362OWSA - IG TVSS Duplex Receptacle with Light and Alarm, 20A 125V, 5-20R, Office White](#)
- [HBL415S - 4-PLEX Surge Suppression Receptacle, 2- Pole 3-Wire, 15A 125V, 5-15R, Blue](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-IG5262OWSA-SPEC-EN | REV 5/2023