



Hospital Grade Surge Suppression Receptacle, Isolated Ground, 15A 125V, 5-15R, Orange

By Hubbell Wiring Device-Kellems
Catalog # [IG8262OSA](#)



Hospital Grade Surge Suppression Receptacle, Isolated Ground, 15A 125V, 5-15R, Orange

Features

- High-impact nylon face resists breakage
- Automatic grounding clip attached to bridge
- Power-on indicator light verifies instantly that power is available
- Distinctive surge symbol for visual identification of surge suppression receptacle

Application

Decorator Duplex with Light and Alarm

General

Color	Orange
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED and Audible Alarm
Item Type	Surge Protection Receptacles
Material	Composite
Material - Mounting Hardware	Mounting Screws
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade
Performance	<ul style="list-style-type: none"> • Electrical - Frequency - 60Hz • Electrical - Protection Modes - Normal and Common Modes • Electrical - Response Time - Approximately 5 ns • Electrical - Transient Suppression - Peak Energy (10 X 100 μs) Peak Current (8 X 20 μs) • Electrical - Voltage - 120V AC + 10% - 15% • Environmental - Flammability - UL 94V-2 • Environmental - Operating Temperature - 32°F to 140°F (0°C to 60°C)

Response Time 5
Series Hospital Grade

Dimensions

Display Size Standard

Electrical Ratings

Amperage Rating	15 A
Connectivity	Terminal Screws
Current / Amperage Rating	15 A
Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

Certifications and Compliance

- | | |
|----------------------|---|
| Industry Standard(s) | <ul style="list-style-type: none"> • CSA Certified to Specification C22.2 No. 42 • Listed to UL Standards 498 Receptacles • UL Listed File E2186 |
|----------------------|---|

Nema Rating 5-15R

Logistics

Carton Quantity 10

Product Assets

- [Catalog Page - Wiring M16 Catalog page](#)
- [Catalog Page - Wiring N-13 Catalog page](#)
- [Catalogs - Wiring Full Catalog](#)
- [Engineering Drawing - IG8262OSA AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD1152_INSTALLINST](#)
- [Literature - WLBD026_Duct Products Brochure_WEB](#)
- [Literature - SpikeShield® Power Quality Surge Protective Devices](#)
- [Sales Drawings - WDK_IG8262_DRAWING_PDF](#)
- [Warranty - Industrial & Commercial Products](#)

Related Products

- [P8OR - Wallplate, 1-Gang, 1\) Duplex, Orange](#)
- [HBL5260OWSA - Surge Protective Devices, SPIKESHIELD TVSS Duplex Receptacle with Light, 15A 125V, 5-15R, Office White](#)
- [IG8362OSA - Hospital Grade Surge Suppression Receptacle, 20A 125V, 5-20R, Office White](#)
- [SS8 - Wallplates and Boxes, Metallic Plates, 1- Gang, 1\) Duplex Opening, Standard Size, Stainless Steel](#)
- [HBI 415S - 4-PI EX Surge Suppression Receptacle, 2- Pole 3-](#)

Style
Type
UPC

Isolated Ground
Duplex
783585060897

WDE455 4P LEX Surge Suppression Receptacle, 2 Pole 3
Wire, 15A 125V, 5-15R, Blue



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-IG8262OSA-SPEC-EN | REV 5/2023