



# Surge Protective Devices, SPIKESHIELD Hospital Grade Surge Suppression Receptacle, 20A 125V, 5-20R, Ivory

By Hubbell Wiring Device-Kellems  
Catalog # IG8362ISA



Surge Protective Devices, SPIKESHIELD Hospital Grade Surge Suppression Receptacle, 20A 125V, 5-20R, Ivory

## Features

- High-impact nylon face resists breakage
- Automatic grounding clip attached to bridge
- Power-on indicator light verifies instantly that power is available
- Distinctive surge symbol provides quick visual identification of surge suppression receptacle

## Application

Decorator Duplex with Light and Alarm

## General

|                              |  |
|------------------------------|--|
| Color                        | Ivory  |
| Environmental Conditions     | Indoor Dry Unless Protected By Additional Means  |
| Indicator(s) Type            | LED and Audible Alarm  |
| Item Type                    | Surge Protection Receptacles   |
| Material                     | Composite  |
| Material - Mounting Hardware | Mounting Screws  |
| OEM Brand Name               | Hubbell Wiring Device-Kellems  |
| Operating Temperature        | 32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)  |
| Outlet                       | Straight Blade   |
| Performance                  | <ul style="list-style-type: none"> <li>• Electrical - Frequency - 60Hz</li> <li>• Electrical - Protection Modes - Normal and Common Modes</li> <li>• Electrical - Response Time - Approximately 5 ns</li> <li>• Electrical - Transient Suppression - Peak Energy (10 X 100 <math>\mu</math>s) Peak Current (8 X 20 <math>\mu</math>s)</li> <li>• Electrical - Voltage - 120V AC + 10% - 15%</li> <li>• Environmental - Flammability - UL 94V-2</li> <li>• Environmental - Operating Temperature - 32°F to 140°F (0°C to 60°C)</li> </ul> |
| Response Time                | 5  |

## Dimensions

Display Size Standard

## Electrical Ratings

|                            |                 |
|----------------------------|-----------------|
| Amperage Rating            | 20 A            |
| Connectivity               | Terminal Screws |
| Current / Amperage Rating  | 20 A            |
| Current Rating             | 20 A            |
| Frequency Rating           | 60 Hz           |
| Phase                      | Single Phase    |
| Voltage Rating             | 125 V           |
| Voltage Rating Description | 125 V           |

## Certifications and Compliance

- |                      |   |
|----------------------|---|
| Industry Standard(s) | <ul style="list-style-type: none"> <li>• CSA Certified to Specification C22.2 No. 42</li> <li>• Listed to UL Standards 498 Receptacles</li> <li>• UL Listed File E2186</li> </ul> |
|----------------------|---|

Nema Rating 5-20R

## Logistics

Carton Quantity 10

## Product Assets

- [Catalog Page - Wiring M16 Catalog page](#)
- [Catalog Page - Wiring N-13 Catalog page](#)
- [Catalogs - Wiring Full Catalog](#)
- [Engineering Drawing - IG8362ISA AutoCAD Drawing](#)
- [Installation Manuals - WIRING\\_PD1152\\_INSTALLINST](#)
- [Literature - WLBD026\\_Duct Products Brochure\\_WEB](#)
- [Literature - SpikeShield® Power Quality Surge Protective Devices](#)
- [Sales Drawings - WDK\\_IG8362\\_DRAWING\\_PDF](#)
- [Warranty - Industrial & Commercial Products](#)

## Related Products

- P8I - Wallplate, 1-Gang, 1) Duplex, Ivory
- HBL5360ISA - Surge Protective Devices, SPIKESHIELD TVSS Duplex Receptacle with Light, 20A 125V, 5-20R, Ivory
- SS8 - Wallplates and Boxes, Metallic Plates, 1- Gang, 1) Duplex Opening, Standard Size, Stainless Steel
- HBL420IS - Surge Protective Devices, 4-PLEX, Surge Suppression Receptacle, 20A 125V, 2-Pole 3-Wire Grounding,

Series  
Style  
Type  
UPC

Hospital Grade  
Isolated Ground  
Duplex  
783585060934

5-20R, Ivory.  
IG8262ISA - Hospital Grade Surge Suppression Receptacle,  
Isolated Ground, 15A 125V, 5-15R, Ivory



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
WDK-IG8362ISA-SPEC-EN | REV 5/2023