

Hospital Grade Surge Suppression Receptacle, 20A 125V, 5-20R, Office White

By Hubbell Wiring Device-Kellems Catalog # IG8362OSA

Hospital Grade Surge Suppression Receptacle, 20A 125V, 5-20R, Office White



Features

- · High-impact nylon face resists breakage
- · Automatic grounding clip attached to bridge
- Power-on indicator light verifies instantly that power is available
- Distinctive surge symbol provides quick visual identification of surge suppression receptacle

Application

Decorator Duplex with Light and Alarm

General

Color	Orange
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED and Audible Alarm
Item Type	Surge Protection Receptacles
Material	Composite
Material - Mounting Hardware	Mounting Screws
OEM Brand Name	Hubbell Wiring Device- Kellems
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade
Performance	• Electrical - Frequency - 60Hz

• Electrical - Protection

Common Modes

 $(8 \times 20 \mu s)$

AC + 10% - 15%

· Environmental -

Modes - Normal and

• Electrical - Response Time

Suppression - Peak Energy

(10 X 100 μ s) Peak Current

• Electrical - Voltage - 120V

Flammability - UL 94V-2

 Environmental - Operating Temperature - 32°F to

140°F (0°C to 60°C)

- Approximately 5 ns Electrical - Transient

Dimensions

Display Size Standard

Electrical Ratings

Amperage Rating 20 A

Connectivity Terminal Screws

Current / Amperage Rating 20 A
Current Rating 20 A
Frequency Rating 60 Hz
Phase Single Phase

Voltage Rating 125 V Voltage Rating Description 125 V

Certifications and Compliance

Industry Standard(s) • CSA Certified to

Specification C22.2 No. 42

• Listed to UL Standards 498

Receptacles
• UL Listed File E2186

Nema Rating 5-20R

Logistics

Carton Quantity 10

Product Assets

Catalog Page - Wiring M16 Catalog page Catalog Page - Wiring N-13 Catalog page

Catalogs - Wiring Full Catalog

Engineering Drawing - IG8362OSA AutoCAD Drawing Installation Manuals - WIRING_PD1152_INSTALLINST Literature - WLBD026_Duct Products Brochure_WEB Literature - SpikeShield® Power Quality Surge Protective

Sales Drawings - WDK_IG8362_DRAWING_PDF Warranty - Industrial & Commercial Products

Related Products

SS8 - Wallplates and Boxes, Metallic Plates, 1- Gang, 1) Duplex Opening, Standard Size, Stainless Steel

IG5262OSA - Surge Protective Devices, SPIKESHIELD IG TVSS Duplex Receptacle with Light and Alarm, 15A 125V, 5-15R, Orange

HBL5360OWSA - Surge Protective Devices, SPIKESHIELD TVSS Duplex Receptacle with Light, 20A 125V, 5-20R, Office White

Response Time 5 IG5362OSA - Surge Protective Devices, SPIKESHIELD IG TVSS

Series Hospital Grade
Style Isolated Ground
Type Duplex
UPC 783585060941

Duplex Receptacle with Light and Alarm, 20A 125V, 5-20R, Orange
HBL420S - Surge Protective Devices, 4-PLEX, Surge
Suppression Receptacle, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Blue.



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved. WDK-IG8362OSA-SPEC-EN | REV 5/2023