



# Signal and Control, Micro-Quick, Female Plug, 3-Pole, LED Cable, 15M Length

By Hubbell Wiring Device-Kellems  
Catalog # [MCMPS13115](#)

Signal and Control, Micro-Quick, Female Plug, 3-Pole, LED Cable, 15M Length



## Application

Quick Connect/Disconnect Signal and Control

## General

Color	Black
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	Angled LED Cable
Jacket	PVC
OEM Brand Name	Hubbell Wiring Device-Kellems
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585524504

## Dimensions

Diameter Live Part	.67"
Length	590.551 in

## Conductor Related

Conductor Type	Copper
Number Of Conductors	3-Pole

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Installation Manuals - WIRING\\_PD1545\\_INSTALLINST](#)  
[Literature - WIRING\\_WLFVM034](#)  
[Literature - Pulp & Paper Solutions](#)  
[Sales Drawings - WDK\\_MCMPS13115\\_DRAWING\\_PDF](#)  
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
WDK-MCMPS13115-SPEC-EN | REV 5/2023