

Multi-Hole Cord Grip Connector

By Hubbell Wiring Device-Kellems  
Catalog # [MHC1032CR](#)



(4) Holes 0.23-0.29" (5.8-7.4mm), 3/4" NPT, Gray Nylon

Features

- Nylon cord connector resists most common industrial corrosives
- Ergonomic design makes them easy to handle and maintain UL listing by hand tightening
- Internal bushing accomodates up to four individual conductors

Application

Terminating Portable Cords into an Enclosure

Performance

Withstands 100lbs of pullout force

General

Catalog Number	MHC1032CR
Color	Gray
Environmental Conditions	Hazardous Locations - Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 in accordance with the NEC
Series	Multi-Hole Cord Grip
Style	Cord Connector

Temperature Rating	-30°F to +225°F (-34°C to +107°C)
Type	Straight Male
UPC	783585708522

Dimensions

Hub Size	3/4" NPT
----------	----------

Conductor Related

Conductor Range	0.23-0.29" (5.8-7.4mm)
Number of Conductors	Up to 4

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	25
-----------------	----

Product Assets

[Catalog Page - WDK W-74](#) [Catalog Page - WDK W-75](#) [Catalog Page - WDK W-76](#)  
[Catalogs - WDK Catalog Full 2024](#)  
[Literature - Multi-Hole Cord Grip Connectors](#)  
[Specifications - MHC1032CR](#)