



# Signal and Control, Micro Quick, Male Plug, Field Attachable, 3-Pole, .16-.24" Cable Range

By Hubbell Wiring Device-Kellems  
Catalog # [MIMS23F7](#)



Signal and Control, Micro Quick, Male Plug, Field Attachable, 3-Pole, .16-.24" Cable Range

## Features

- Body with high impact design
- Strain relief protects terminations
- Precision wire funnels eliminate stray strands

## Application

Quick Connect/Disconnect Signal and Control

## General

EU RoHS Indicator	No
Environmental Conditions	IP67 Ingress Protection
Item Type	Male In-Line Straight Plug
Material - Coupling Nut	Aluminum
Material - Insert	PUR/PA
Material - O-Ring	Neoprene
Material - Overmold	PBT
Material - Shell	PBT
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature Performance	-40 Deg C to 85 Deg C <ul style="list-style-type: none"><li>• Electrical - Amperage - 4A</li><li>• Electrical - Maximum Wire Size - #18 AWG</li><li>• Electrical - Voltage Rating - 250V</li><li>• Environmental - Moisture Resistance - IP66 Suitability</li><li>• Environmental - Operating Temperature - -40°C to 90°C</li></ul>
Thread Size	Non-Threaded
UPC	783585192376

## Electrical Ratings

Amperage Rating	4 A
Current / Amperage Rating	4 A
Current Rating	4 A
Voltage Rating	250V kV

## Conductor Related

Cable Size	.16"-.24"
Cable Specification	UL Listed Portable Cord

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• CSA Certified, C22.2 No. 182.3 and CSA C22.2 No. 94.2-07</li><li>• UL 2238 and UL50E, File No. E192071</li></ul>
----------------------	--

## Logistics

Carton Quantity	30
-----------------	----

## Product Assets

[Literature - WIRING\\_WLFVM034](#)  
[Literature - Pulp & Paper Solutions](#)  
[Sales Drawings - WDK\\_MIMS23F7\\_DRAWING\\_PDF](#)  
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
WDK-MIMS23F7-SPEC-EN | REV 5/2023