

Signal and Control, Linkosity, Power
System Distribution Assembly, 3-
Gang, Spec Grade, with Pass Thru

By Hubbell Wiring Device-Kellems
Catalog # [MSL3SG00P](#)

Signal and Control, Linkosity, Power System Distribution
Assembly, 3-Gang, Spec Grade, with Pass Thru

Features

- Linkosity
- Power System Distribution Assembly
- 3-Gang
- Spec Grade

General

Catalog Number	MSL3SG00P
Color	Gray
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Conduit Feed Pre-Wired Box
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	783585521695

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings



Amperage Rating	20 A
Connectivity	Plug Together
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase Control
Voltage Rating	250V AC Max kV
Wattage	5000

Conductor Related

Number Of Wires	4-Wire Grounding
Wire Size	#12 AWG

Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - MSL3SG00P AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2050_INSTALLINST](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Sales Drawings - WDK_MSL3SG00P_DRAWINGS_PDF](#)
- [Specifications - MSL3SG00P](#)
- [Warranty - Industrial & Commercial Products](#)