

## Nano-Quick Control Connectors, Female Straight 3 Wire, IDC

By Hubbell Wiring Device-Kellems  
Catalog # [NCTS13IDC](#)



Nano-Quick Control Connectors, Female Straight 3 Wire, IDC

### Features

- Strain Relief Bushing Protects terminations
- Wire Guide For virtually toolless termination
- Copper Alloy insulation displacement contacts
- Rugged, Nickel-plated Hardware prevents corrosion

### General

Application	Quick Connect/Disconnect Signal and Control
Catalog Number	NCTS13IDC
Color	Black
EU RoHS Indicator	Yes
Item Type	Female Straight Plug
OEM Brand Name	Hubbell Wiring Device-Kellems
Performance	Electrical - Amperage - 3A  Electrical - Contact Resistance - Less than or Equal to 5 Milliohm  Electrical - Voltage Rating - 32VAC/DC  Electrical - Wire Range - #22 AWG max., #24 AWG min  Environmental - Ingress Protection - IP66 Suitability  Environmental - Operating Temperature - -20°C to 110°C
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585226637

### Dimensions

Diameter Live Part	.38"
--------------------	------

### Conductor Related

Conductor Type	Copper
Number of Conductors	3-Pole

### Certifications And Compliance

Industry Standard(s)	CSA Certified, C22.2 No. 182.3 and CSA C22.2 No. 94.2-07  UL 2238 and UL50E, File No. E1
----------------------	---------------------------------------------------------------------------------------------------

### Logistics

Carton Quantity	25
-----------------	----

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Installation Manuals - WIRING\\_PD1939\\_INSTALLINST](#)  
[Literature - Pulp & Paper Solutions](#)  
[Literature - PULP & PAPER SOLUTIONS](#)  
[Sales Drawings - WDK\\_NCTS13IDC\\_DRAWING\\_PDF](#)  
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK-NCTS131DC-SPEC-EN | REV 6/2024