



Wiring Device-Kellems

Nano-Quick Control Connectors, Male, Straight Plug, 3 Wire, IDC

By Hubbell Wiring Device-Kellems
Catalog # [NITS13IDC](#)



Nano-Quick Control Connectors, Male, Straight Plug, 3 Wire, IDC

Features

- Strain Relief Bushing Protects terminations
- Wire Guide For virtually toolless termination
- Copper Alloy insulation displacement contacts
- Rugged, Nickel-plated Hardware prevents corrosion

Application

Quick Connect/Disconnect Signal and Control

General

Color	Black
EU RoHS Indicator	Yes
Item Type	Male Straight Plug
OEM Brand Name	Hubbell Wiring Device-Kellems
Performance	<ul style="list-style-type: none"> • Electrical - Amperage - 3A • Electrical - Contact Resistance - Less than or Equal to 5 Milliohm • Electrical - Voltage Rating - 32VAC/DC • Electrical - Wire Range - #22 AWG max., #24 AWG min • Environmental - Ingress Protection - IP66 Suitability • Environmental - Operating Temperature - -20°C to 110°C
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585226620

Dimensions

Diameter Live Part .38"

Conductor Related

Conductor Type Copper
Number Of Conductors 3-Pole

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • CSA Certified, C22.2 No. 182.3 and CSA C22.2 No. 94.2-07 • UL 2238 and UL50E, File No. E1
----------------------	--

Logistics

Carton Quantity 25

Product Assets

- [Installation Manuals - WIRING_PD1939_INSTALLINST](#)
- [Literature - WIRING_WLFVM034](#)
- [Literature - Pulp & Paper Solutions](#)
- [Sales Drawings - WDK_NITS13IDC_DRAWING_PDF](#)
- [Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.