

Wallplates and Box Covers, Wallplate, Nylon, 2-Gang, 2) Duplex, Light Almond

By Hubbell Wiring Device-Kellems Catalog # NP82LA

Wallplates and Box Cover, Wallplate, Double, 2-Duplex



- Reinforcement ribs for extra strength
- Captive screw feature holds mounting screw in place
- High-impact, self-extinguishing nylon material

Application

Protection against contact of live terminals and wiring. Provides finished look to installation.

General

Color Light Almond
Construction Molded
Cutout 2) Duplex
EU RoHS Indicator Yes

Item Type Screw Mount

Material Nylon

Material - Mounting Hardware Screw Mounting

Number of Gang(s) 2-Gang

OEM Brand Name Hubbell Wiring Device-

Kellems


Orientation Vertical Mount
Performance • Environmental -

 Environmental -Appearance - Smooth

 Environmental - Operating Temperature - -40°C to

85°C

Size Standard
Style 2-Duplex
Type Duplex
UPC 883778118371



Dimensions

Display Size Standard Sized

Thickness 0.06

Certifications and Compliance

Industry Standard(s) UL Listed

Logistics

Carton Quantity 25

Product Assets

Literature - Residential Product Guide
Sales Drawings - WDK_NP82_DRAWING_PDF
Warranty - tradeSELECT™ and netSELECT®

Related Products

SS78 - Wallplates and Boxes, Metallic Plates, 2- Gang, 1) Duplex 1) 1.40" Openings, Standard Size, Stainless Steel PJ8LA - Wallplate, Mid-Size 1-Gang, 1) Duplex, Light Brown SS138 - Wallplates and Boxes, Metallic Plates, 2- Gang, 1 Blank 1) Duplex Opening, Standard Size, Stainless Steel P28LA - Wallplate, 3-Gang, 2) Toggle 1) Duplex, Light Almond SS82 - Wallplates and Boxes, Metallic Plates, 2- Gang, 2) Duplex Openings, Standard Size, Stainless Steel

