



## Snap-In, F Coax, Nickel, Black

By Hubbell Wiring Device-Kellems  
Catalog # [NSF70BK](#)

Snap-In, F Coax, Nickel, Black



### Application

CATV

### General

Contact	Phosphor Bronze
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	1) Nickel F-Coax Connector
Material - Mounting Hardware	Screw Mounting
Style	Coupler
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	F-Type
UPC	883778503283

### Dimensions

Display Size Standard Sized Product

### Electrical Ratings

Connectivity	Female to Female
Contact Resistance	Per TIA
Insertion Loss	Per TIA

### Logistics

Carton Quantity 25

### Product Assets

[Catalog Page - Wiring AA-10 Catalog Page](#)  
[Catalog Page - Wiring\\_Catalog\\_Z6\\_CatPage](#)  
[Catalogs - Wiring Full Catalog](#)  
[Engineering Drawing - NSF70BK AutoCAD Drawing](#)  
[Sales Drawings - WDK\\_NSF70\\_DRAWING\\_PDF](#)  
[Warranty - Industrial & Commercial Products](#)

### Related Products

[SFFBX - Snap-Fit, F-Coax Connector, Black](#)  
[NSF70W - Net Select, Snap-Fit, With F Connector, White](#)  
[NSF70LA - Net Select, Snap-Fit, With F Connector, Light Almond](#)  
[SFF3GBK - F Coax, Snap-Fit, 3GHz, Gold, Black](#)  
[SFRFGBK - Connector, Snap-Fit, RCA to F-Coupler, Black](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
WDK-NSF70BK-SPEC-EN | REV 5/2023