



Snap-In, F Coax, Nickel, Gray

By Hubbell Wiring Device-Kellems
Catalog # [NSF70GY](#)

Snap-In, F Coax, Nickel, Gray



Features

- Universal keystone design
- Seamless Hubbell system integration
- Quick and easy screw-style installation

Application

CATV

General

Contact	Phosphor Bronze
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	1) Nickel F-Coax Connector
Material - Mounting Hardware	Screw Mounting
Style	Coupler
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	F-Type
UPC	883778503306

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Connectivity	Female to Female
Contact Resistance	Per TIA
Insertion Loss	Per TIA

Logistics

Carton Quantity 25

Product Assets

[Catalog Page - PREM S9 CatalogPage](#)
[Catalog Page - WDK Y-6 Catalog Page](#)
[Catalog Page - WDK Z-10 Catalog Page](#)
[Catalogs - Premise Wiring Catalog](#)
[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - NSF70GY AutoCAD Drawing](#)
[Sales Drawings - WDK_NSF70_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK-NSF70GY-SPEC-EN | REV 5/2024