

# Marine, Incandescent Light Fixture

By Hubbell Wiring Device-Kellems Catalog # NVA15GHGA

Marine, Incandescent Light Fixture



## **Application**

Marine Lighting

#### General

Ballast/Driver Manufacturer None Color Gray

Item Type Pendant Mounted Vaportight

Lamp IncludedNoLamp TypeA LampMaterialCompositeMaterial - Mounting HardwareScrew Mounting

Number of Lamps 1

OEM Brand Name Hubbell Wiring Device-

Kellems

Performance Environmental - Operating

Temperature - -40°F (-40°C)

to +302°F (150°)

 Socket Type
 Medium Base

 Style
 Vapor Tight

 UPC
 783585357355

### **Dimensions**

Length 11.8 in Width 5.9 in

# **Electrical Ratings**

Amperage Rating 1.2 A
Current / Amperage Rating 1.2 A
Frequency Rating 50-60 Hz
Voltage Rating 125 VAC
Wattage 150 W

## **Certifications and Compliance**

Industry Standard(s) • UL 1598 Standard

UL1571 ListedUL595 Listed

# Logistics

Carton Quantity 5

### **Product Assets**

Catalog Page - Wiring\_Catalog\_BB51\_CatPage

Catalogs - Wiring Full Catalog

Engineering Drawing - NVA15GHGA AutoCAD Drawing

Literature - Hubbell Marine Full Line Catalog

Sales Drawings - WDK\_NVA15GHGA\_DRAWING\_PDF

Warranty - Industrial & Commercial Products

### **Related Products**

VCGP100 - Lighting Fixture, Glass Globe, Replacement Marine Lighting Fixture.

 $\ensuremath{\mathsf{NVBA}}$  - Marine Wiring Products, Wall Mounting Bracket for  $\ensuremath{\mathsf{NVX15GHGA}}$ 

NVX15GHGA - Marine Wiring Products, Non-Metallic

Vaportight Fixture

 $\ensuremath{\mathsf{NVGA}}$  - Marine Wiring Products, Replacement Guard for  $\ensuremath{\mathsf{NVX}}$  and  $\ensuremath{\mathsf{NVA15GHGA}}$ 

