

# Signal And Control, Panel Safe, 1) DH485, 1) 15A 125V Receptacle, NEMA 12/4 Enclosure

By Hubbell Wiring Device-Kellems

Catalog # [P15DH485C10](#)

Signal And Control, Panel Safe, 1) DH485, 1) 15A 125V Receptacle, NEMA 12/4 Enclosure



## Features

- 
- 
- 
- 

## General

Catalog Number	P15DH485C10
Color	Gray, Clear
EU RoHS Indicator	Yes
Enclosure Type	NEMA 12/4
Item Type	Industrial Connectivity
Material	Composite
Material - Mounting Hardware	Screw Mounting
OEM Brand Name	Hubbell Wiring Device-Kellems
Performance	Electrical - Circuit Breaker - 3A Electrical - Data Jack - Cat. 5e Electrical - GFCI - Conforms to UL 943 2006 requirement Electrical - In-Cabinet Receptacle - GFCI protected Environmental - Enclosure - NEMA Type 4, 12 and NEMA Type 4X
UPC	783585093482

## Dimensions

Cubic Capacity	34.375 cu.in
Depth	2.5
Height	5.5 in
Width	2.5 in

## Conductor Related

Cable Entry	Plug-In
-------------	---------

## Certifications And Compliance

Industry Standard(s)	CSA Certified UL Recognized
----------------------	--------------------------------

## Logistics

Carton Quantity	20
-----------------	----

## Product Assets

- [Catalog Page - WDK I-15 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - P15DH485C10 AutoCAD Drawing](#)
- [Installation Manuals - WIRING\\_PD2170\\_INSTALLINST](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Sales Drawings - WDK\\_P15DH485C10\\_DRAWING\\_PDF](#)
- [Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK-P15DH485C10-SPEC-EN | REV 6/2024