



Wiring Device-Kellems

# Signal And Control, Linkosity, Cordset, Female, Single End, Straight, 3-Wire, 10A 600V AC, PB Wire Code, 5' Length, Stainless Hex Nuts



By Hubbell Wiring Device-Kellems  
Catalog # [PF1003PB005S](#)

Signal And Control, Linkosity, Cordset, Female, Single End, Straight, 3-Wire, 10A 600V AC, PB Wire Code, 5' Length, Stainless Hex Nuts

### Application

Quick Connect/Disconnect Signal and Control

### General

Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	Single Ended Cable, Straight Female Connector
OEM Brand Name	Hubbell Wiring Device-Kellems
Plug Type	Linkosity
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585243245

### Dimensions

Outside Diameter	0.71
------------------	------

### Electrical Ratings

Amperage Rating	10 A
Current / Amperage Rating	10 A
Current Rating	10 A
Voltage Rating	600V kV

### Conductor Related

Conductor Size	#12 AWG
Conductor Type	Copper
Number Of Conductors	3-Pole
Strands	Multi

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

- [Installation Manuals - WIRING\\_PD2038\\_INSTALLINST](#)
- [Literature - WIRING\\_WLFVM034](#)
- [Literature - Linkosity Wiring System](#)
- [Literature - Pulp & Paper Solutions](#)
- [Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.