

Signal And Control, Linkosity, Cordset, Female, Single End, Straight, 3-Wire, 10A 600V AC, PB Wire Code, 15' Length

By Hubbell Wiring Device-Kellems
Catalog # [PF1003PB015](#)

Signal And Control, Linkosity, Cordset, Female, Single End,
Straight, 3-Wire, 10A 600V AC, PB Wire Code, 15' Length

Features

- Linkosity
- Cordset
- Female
- Single End

Application

Quick Connect/Disconnect Signal and Control

General

| | |
|--------------------|--------------------------------------|
| Catalog Number | PF1003PB015 |
| Color | Gray |
| EU RoHS Indicator | Yes |
| Insulation | PVC |
| Item Type | Female Plug Single Ended Straight |
| Jacket | PVC |
| OEM Brand Name | Hubbell Wiring Device-Kellems |
| Temperature Rating | -20 Deg C to 105 Deg C |
| UPC | 783585358307 |



Dimensions

Diameter Live Part .46"

Conductor Related

Conductor Type Copper
Number of Conductors 3-Pole

Logistics

Carton Quantity 10

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Installation Manuals - WIRING_PD2038_INSTALLINST](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Literature - Pulp & Paper Solutions](#)
[Literature - Linkosity Wiring System](#)
[Specifications - PF1003PB015](#)
[Warranty - Industrial & Commercial Products](#)