

Linkosity, Female Cable, 3W, 60'

By Hubbell Wiring Device-Kellems
Catalog # [PF1003PB060](#)

Linkosity, Female Cable, 3W, 60'



General

Application	Quick Connect/Disconnect Signal and Control
Catalog Number	PF1003PB060
Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	Single Ended Cable, Straight Female Connector
OEM Brand Name	Hubbell Wiring Device-Kellems
Plug Type	Linkosity
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585524009

Dimensions

Outside Diameter	0.71
------------------	------

Electrical Ratings

Amperage Rating	10 A
Current / Amperage Rating	10 A
Current Rating	10 A
Voltage Rating	600V kV

Conductor Related

Conductor Size	#12 AWG
Conductor Type	Copper
Number of Conductors	3-Pole
Strands	Multi

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Installation Manuals - WIRING_PD2038_INSTALLINST](#)
[Literature - Pulp & Paper Solutions](#)
[Literature - Linkosity Wiring System](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand