



Wiring Device-Kellems

Signal And Control, Linkosity, Cordset, Female, Single End, Straight, 4-Wire, 10A 600V AC, PA Wire Code, 30' Length

By Hubbell Wiring Device-Kellems
Catalog # [PF1004PA030](#)



Signal And Control, Linkosity, Cordset, Female, Single End, Straight, 4-Wire, 10A 600V AC, PA Wire Code, 30' Length

Application

Quick Connect/Disconnect Signal and Control

General

Color	Gray
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	Female Plug Single Ended Straight
Jacket	PVC
OEM Brand Name	Hubbell Wiring Device-Kellems
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585243047

Dimensions

Diameter Live Part	.46"
--------------------	------

Conductor Related

Conductor Type	Copper
Number Of Conductors	4-Pole

Logistics

Carton Quantity	5
-----------------	---

Product Assets

- [Installation Manuals - WIRING_PD2038_INSTALLINST](#)
- [Literature - WIRING_WLFVM034](#)
- [Literature - Linkosity Wiring System](#)
- [Literature - Pulp & Paper Solutions](#)
- [Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.