

# Signal And Control, Linkosity, Cordset, Female, Single End, Straight, 12-Wire, 7A 600V AC, PE Wire Code, 5' Length

By Hubbell Wiring Device-Kellems  
Catalog # [PF1012PE005](#)



Signal And Control, Linkosity, Cordset, Female, Single End, Straight, 12-Wire, 7A 600V AC, PE Wire Code, 5' Length

## General

Application	Quick Connect/Disconnect Signal and Control
Catalog Number	PF1012PE005
Color	Gray
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	Female Plug Single Ended Straight
Jacket	PVC
OEM Brand Name	Hubbell Wiring Device-Kellems
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585128238

## Dimensions

Diameter Live Part	.46"
--------------------	------

## Conductor Related

Conductor Type	Copper
Number of Conductors	12-Pole

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Installation Manuals - WIRING\\_PD2038\\_INSTALLINST](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - Linkosity Wiring System](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Warranty - Industrial & Commercial Products](#)