



Linkosity, Female Cable 10A, 12P, 50'

By Hubbell Wiring Device-Kellems
Catalog # [PF1012PE050](#)



Linkosity, Female Cable 10A, 12P, 50'

Application

Quick Connect/Disconnect Signal and Control

General

Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	Single Ended Cable, Straight Female Connector
OEM Brand Name	Hubbell Wiring Device-Kellems
Plug Type	Linkosity
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585116365

Dimensions

Outside Diameter	0.89
------------------	------

Electrical Ratings

Amperage Rating	7 A
Current / Amperage Rating	7 A
Current Rating	7 A
Voltage Rating	600V kV

Conductor Related

Conductor Size	#12 AWG
Conductor Type	Copper
Number Of Conductors	12-Pole
Strands	Multi

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Installation Manuals - WIRING_PD2038_INSTALLINST](#)
[Literature - WIRING_WLFVM034](#)
[Literature - Linkosity Wiring System](#)
[Literature - Pulp & Paper Solutions](#)
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-PF1012PE050-SPEC-EN | REV 5/2023