

HUBBELL
Wiring Device-Kellems

Signal And Control, Linkosity, Cordset, Female, Double End, 90 Degree, 3-Wire, 10A 600V AC, PB Wire Code, 15' Length

By Hubbell Wiring Device-Kellems
Catalog # [PG1003PB015](#)

Signal And Control, Linkosity, Cordset, Female, Double End, 90
Degree, 3-Wire, 10A 600V AC, PB Wire Code, 15' Length



General

Application	Quick Connect/Disconnect Signal and Control
Catalog Number	PG1003PB015
Color	Gray
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	Female Plug Single Ended Angled
Jacket	PVC
OEM Brand Name	Hubbell Wiring Device-Kellems
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585454085

Dimensions

Diameter Live Part	.46"
--------------------	------

Conductor Related

Conductor Type	Copper
Number of Conductors	3-Pole

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Installation Manuals - WIRING_PD2038_INSTALLINST](#)
[Literature - Pulp & Paper Solutions](#)
[Literature - Linkosity Wiring System](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Warranty - Industrial & Commercial Products](#)