



# Signal And Control, Linkosity, Cordset, Female, Double End, 90 Degree, 4-Wire, 10A 600V AC, PA Wire Code, 5 'Length

By Hubbell Wiring Device-Kellems  
Catalog # [PG1004PA005](#)



Signal And Control, Linkosity, Cordset, Female, Double End, 90 Degree, 4-Wire, 10A 600V AC, PA Wire Code, 5 'Length

## Application

Quick Connect/Disconnect Signal and Control

## General

Color	Gray
Construction	Fabricated
EU RoHS Indicator	No
Insulation	PVC
Item Type	Single Ended Cable, 90 Degree Female Connector
OEM Brand Name	Hubbell Wiring Device-Kellems
Plug Type	Linkosity
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585454177

## Dimensions

Outside Diameter	0.75
------------------	------

## Electrical Ratings

Amperage Rating	10 A
Current / Amperage Rating	10 A
Current Rating	10 A
Voltage Rating	600V kV

## Conductor Related

Conductor Size	#12 AWG
Conductor Type	Copper
Number Of Conductors	4-Pole
Strands	Multi

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Installation Manuals - WIRING\\_PD2038\\_INSTALLINST](#)  
[Literature - WIRING\\_WLFVM034](#)  
[Literature - Linkosity Wiring System](#)  
[Literature - Pulp & Paper Solutions](#)  
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
WDK-PG1004PA005-SPEC-EN | REV 5/2023