

HUBBELL
Wiring Device-Kellems

Signal And Control, Linkosity, Cordset, Female, Double End, 90 Degree, 7-Wire, 10A 600V AC, PE Wire Code, 20' Length

By Hubbell Wiring Device-Kellems
Catalog # [PG1007PE020](#)

Signal And Control, Linkosity, Cordset, Female, Double End, 90 Degree, 7-Wire, 10A 600V AC, PE Wire Code, 20' Length



General

Application	Quick Connect/Disconnect Signal and Control
Catalog Number	PG1007PE020
Color	Gray
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	Female Plug Single Ended Angled
Jacket	PVC
OEM Brand Name	Hubbell Wiring Device-Kellems
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585454115

Dimensions

Diameter Live Part	.46"
--------------------	------

Conductor Related

Conductor Type	Copper
Number of Conductors	7-Pole

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Installation Manuals - WIRING_PD2038_INSTALLINST](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - Linkosity Wiring System](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Warranty - Industrial & Commercial Products](#)