

Signal And Control, Linkosity,  
Cordset, Female, Double End, 90  
Degree, 7-Wire, 10A 600V AC, PE  
Wire Code, 20' Length

By Hubbell Wiring Device-Kellems  
Catalog # [PG1007PE020](#)

Signal And Control, Linkosity, Cordset, Female, Double End, 90  
Degree, 7-Wire, 10A 600V AC, PE Wire Code, 20' Length

Features

- Linkosity
- Cordset
- Female
- Double End

Application

Quick Connect/Disconnect Signal and Control

General

Catalog Number	PG1007PE020
Color	Gray
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	Female Plug Single Ended Angled
Jacket	PVC
OEM Brand Name	Hubbell Wiring Device-Kellems
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585454115



Dimensions

Diameter Live Part	.46"
--------------------	------

Conductor Related

Conductor Type	Copper
Number of Conductors	7-Pole

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Installation Manuals - WIRING\\_PD2038\\_INSTALLINST](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - Linkosity Wiring System](#)
- [Specifications - PG1007PE020](#)
- [Warranty - Industrial & Commercial Products](#)