



# Signal And Control, Linkosity, Cordset, Female, Double End, 90 Degree, 10-Wire, 10A 600V AC, PE Wire Code, 20' Length

By Hubbell Wiring Device-Kellems  
Catalog # [PG1010PE020](#)



Signal And Control, Linkosity, Cordset, Female, Double End, 90 Degree, 10-Wire, 10A 600V AC, PE Wire Code, 20' Length

## Application

Plug Together Power Distribution, No Pass Thru

## General

Color	Gray
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Conduit Feed Pre-Wired Box
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	10-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	783585185064

## Dimensions

Display Size	Standard Sized Product
--------------	------------------------

## Electrical Ratings

Amperage Rating	5 A
Connectivity	Plug Together
Current / Amperage Rating	5 A
Current Rating	5 A
Phase	Single Phase Control
Voltage Rating	250V AC Max kV
Wattage	1250

## Conductor Related

Number Of Wires	11-Wire Grounding
Wire Size	#12 AWG

## Certifications and Compliance

Nema Rating	Non-NEMA
-------------	----------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Installation Manuals - WIRING\\_PD2038\\_INSTALLINST](#)  
[Literature - WIRING\\_WLFVM034](#)  
[Literature - Linkosity Wiring System](#)  
[Literature - Pulp & Paper Solutions](#)  
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
WDK-PG1010PE020-SPEC-EN | REV 5/2023