



## Linkosity, 20A Single Female Right Angle Cable, 5'

By Hubbell Wiring Device-Kellems  
Catalog # [PG2304PB005](#)

Linkosity, 20A Single Female Right Angle Cable, 5'



### Application

Quick Connect/Disconnect Signal and Control

### General

Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	Single Ended Cable, 90 Degree Female Connector
OEM Brand Name	Hubbell Wiring Device-Kellems
Plug Type	Linkosity
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585116761

### Dimensions

Outside Diameter	0.75
------------------	------

### Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Current Rating	20 A
Voltage Rating	600V kV

### Conductor Related

Conductor Size	#12 AWG, #10 AWG Neutral
Conductor Type	Copper
Number Of Conductors	4-Pole
Strands	Multi

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Engineering Drawing - PG2304PB005 AutoCAD Drawing](#)  
[Installation Manuals - WIRING\\_PD1996\\_INSTALLINST](#)  
[Literature - WIRING\\_WLFVM034](#)  
[Literature - Linkosity Wiring System](#)  
[Literature - Pulp & Paper Solutions](#)  
[Sales Drawings - WDK\\_PG2304PB005\\_DRAWING\\_PDF](#)  
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
WDK-PG2304PB005-SPEC-EN | REV 5/2023