

Linkosity, 30A Female Right Angle
Cable, 10'

By Hubbell Wiring Device-Kellems
Catalog # [PG3004PA010](#)

Linkosity, 30A Female Right Angle Cable, 10'

Features

- Linkosity
- 30A Female Right Angle Cable
- 10'

Application

Quick Connect/Disconnect Signal and Control

General

Catalog Number	PG3004PA010
Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	Single Ended Cable, 90 Degree Female Connector
OEM Brand Name	Hubbell Wiring Device-Kellems
Plug Type	Linkosity
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585116808

Dimensions

Outside Diameter	0.75
------------------	------

Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A
Current Rating	30 A
Voltage Rating	600V kV

Conductor Related

Conductor Size	#10 AWG
Conductor Type	Copper
Number of Conductors	4-Pole
Strands	Multi

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - PG3004PA010 AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2034_INSTALLINST](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - Linkosity Wiring System](#)
- [Sales Drawings - WDK_PG3004PA010_DRAWING_PDF](#)
- [Specifications - PG3004PA010](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Linkosity®](#)

