

Signal And Control, Linkosity,
Cordset, Male, Single Ended,
Straight, 4-Wire, 10A 600V AC, PA
Wire Code, 5 'Length

By Hubbell Wiring Device-Kellems
Catalog # [PM1004PA005](#)

Signal And Control, Linkosity, Cordset, Male, Single Ended,
Straight, 4-Wire, 10A 600V AC, PA Wire Code, 5 'Length

Features

- Linkosity
- Cordset
- Male
- Single Ended

Application

Plug Together Power Distribution, No Pass Thru

General

Catalog Number	PM1004PA005
Color	Gray
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Conduit Feed Pre-Wired Box
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	783585185040

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	10 A
Connectivity	Plug Together
Current / Amperage Rating	10 A
Current Rating	10 A
Phase	Single Phase Control
Voltage Rating	250V AC Max kV
Wattage	2500

Conductor Related

Number Of Wires	4-Wire Grounding
Wire Size	#12 AWG

Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Installation Manuals - WIRING_PD2038_INSTALLINST](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Literature - Pulp & Paper Solutions](#)
[Literature - Linkosity Wiring System](#)
[Specifications - PM1004PA005](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Linkosity®](#)

