

Signal And Control, Linkosity, Cordset, Male, Single Ended, Straight, 4-Wire, 10A 600V AC, PB Wire Code, 35' Length

By Hubbell Wiring Device-Kellems
Catalog # [PM1004PB035](#)



Signal And Control, Linkosity, Cordset, Male, Single Ended, Straight, 4-Wire, 10A 600V AC, PB Wire Code, 35' Length

General

Application	Heavy Duty Industrial
Catalog Number	PM1004PB035
Color	Gray
EU RoHS Indicator	Yes
Environmental Conditions	Wet and Damp Locations
Item Type	Male Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	783585184982

Dimensions

Display Size	Linkosity
--------------	-----------

Electrical Ratings

Amperage Rating	10 A
Connectivity	Pre-Terminated
Current / Amperage Rating	10 A
Current Rating	10 A
Phase	Single Phase
Voltage Rating	600V AC kV
Wattage	6000

Conductor Related

Number Of Wires	4-Wire Grounding
Wire Size	Pre-Terminated

Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

Logistics

Carton Quantity	5
-----------------	---

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Installation Manuals - WIRING_PD2038_INSTALLINST](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - Linkosity Wiring System](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK-PM1004PB035-SPEC-EN | REV 6/2024