

Signal And Control, Linkosity, Cordset, Male, Single Ended, Straight, 5-Wire, 20A 600V AC, PA Wire Code, 30' Length

By Hubbell Wiring Device-Kellems
Catalog # [PM2005PA030](#)



Signal And Control, Linkosity, Cordset, Male, Single Ended, Straight, 5-Wire, 20A 600V AC, PA Wire Code, 30' Length

General

Application	Quick Connect/Disconnect Signal and Control
Catalog Number	PM2005PA030
Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	Single Ended Cable, Straight Male Connector
OEM Brand Name	Hubbell Wiring Device-Kellems
Plug Type	Linkosity
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585358116

Dimensions

Outside Diameter	0.75
------------------	------

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Current Rating	20 A
Voltage Rating	600V kV

Conductor Related

Conductor Size	#12 AWG
Conductor Type	Copper
Number of Conductors	5-Pole
Strands	Multi

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Installation Manuals - WIRING_PD2032_INSTALLINST](#)
[Literature - Pulp & Paper Solutions](#)
[Literature - Linkosity Wiring System](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand