



Linkosity, 20A Single Male Cable, 10'

By Hubbell Wiring Device-Kellems
Catalog # [PM2304PB010](#)



Linkosity, 20A Single Male Cable, 10'

Application

Quick Connect/Disconnect Signal and Control

General

Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	Single Ended Cable, Straight Male Connector
OEM Brand Name	Hubbell Wiring Device-Kellems
Plug Type	Linkosity
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585116891

Dimensions

Outside Diameter	0.75
------------------	------

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Current Rating	20 A
Voltage Rating	600V kV

Conductor Related

Conductor Size	#12 AWG, #10 AWG Neutral
Conductor Type	Copper
Number Of Conductors	4-Pole
Strands	Multi

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Engineering Drawing - PM2304PB010 AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1996_INSTALLINST](#)
[Literature - WIRING_WLFVM034](#)
[Literature - Linkosity Wiring System](#)
[Literature - Pulp & Paper Solutions](#)
[Sales Drawings - WDK_PM2304PB_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-PM2304PB010-SPEC-EN | REV 5/2023