



Wiring Device-Kellems

Signal And Control, Linkosity, Cordset, Male, Single Ended, Straight, 4-Wire, 20A 600V AC, PA Wire Code, 50' Length



By Hubbell Wiring Device-Kellems
Catalog # [PM3004PA050](#)

Signal And Control, Linkosity, Cordset, Male, Single Ended, Straight, 4-Wire, 20A 600V AC, PA Wire Code, 50' Length

Application

Quick Connect/Disconnect Signal and Control

General

Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	Single Ended Cable, Straight Male Connector
OEM Brand Name	Hubbell Wiring Device-Kellems
Plug Type	Linkosity
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585358024

Dimensions

Outside Diameter	0.75
------------------	------

Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A
Current Rating	30 A
Voltage Rating	600V kV

Conductor Related

Conductor Size	#10 AWG
Conductor Type	Copper
Number Of Conductors	4-Pole
Strands	Multi

Product Assets

- [Engineering Drawing - PM3004PA050 AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2034_INSTALLINST](#)
- [Literature - WIRING_WLFVM034](#)
- [Literature - Linkosity Wiring System](#)
- [Literature - Pulp & Paper Solutions](#)
- [Sales Drawings - WDK_PM3004PA_DRAWING_PDF](#)
- [Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.