



Wiring Device-Kellems

# Signal And Control, Linkosity, Cordset, Male, Single Ended, Straight, 4-Wire, 20A 600V AC, PA Wire Code, 85' Length

By Hubbell Wiring Device-Kellems  
Catalog # [PM3004PA085](#)



Signal And Control, Linkosity, Cordset, Male, Single Ended, Straight, 4-Wire, 20A 600V AC, PA Wire Code, 85' Length

### Application

Quick Connect/Disconnect Signal and Control

### General

Color	Gray
EU RoHS Indicator	No
Insulation	PVC
Item Type	Male Straight Plug
Jacket	PVC
OEM Brand Name	Hubbell Wiring Device-Kellems
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585192949

### Dimensions

Diameter Live Part .46"

### Conductor Related

Conductor Type	Copper
Number Of Conductors	4-Pole

### Product Assets

- [Engineering Drawing - PM3004PA085 AutoCAD Drawing](#)
- [Installation Manuals - WIRING\\_PD2034\\_INSTALLINST](#)
- [Literature - WIRING\\_WLFVM034](#)
- [Literature - Linkosity Wiring System](#)
- [Literature - Pulp & Paper Solutions](#)
- [Sales Drawings - WDK\\_PM3004PA\\_DRAWING\\_PDF](#)
- [Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.