

Signal And Control, Linkosity, Cordset, Male, Single Ended 90 Degree, 3-Wire, 10A 600V AC, PB Wire Code, 10' Length, Stainless Hex Nuts

By Hubbell Wiring Device-Kellems
Catalog # [PN1003PB010S](#)



Signal And Control, Linkosity, Cordset, Male, Single Ended 90 Degree, 3-Wire, 10A 600V AC, PB Wire Code, 10' Length, Stainless Hex Nuts

General

Application	Quick Connect/Disconnect Signal and Control
Catalog Number	PN1003PB010S
Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	Single Ended Cable with Male 90 Degree Connector
OEM Brand Name	Hubbell Wiring Device-Kellems
Plug Type	Linkosity
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585184739

Dimensions

Outside Diameter	0.71
------------------	------

Electrical Ratings

Amperage Rating	10 A
Current / Amperage Rating	10 A
Current Rating	10 A
Voltage Rating	600V kV

Conductor Related

Conductor Size	#12 AWG
Conductor Type	Copper
Number of Conductors	3-Pole
Strands	Multi

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Installation Manuals - WIRING_PD2038_INSTALLINST](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - Linkosity Wiring System](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK-PN1003PB010S-SPEC-EN | REV 6/2024