

Signal And Control, Linkosity,
Cordset, Male, Single Ended 90
Degree, 4-Wire, 10A 600V AC, PA
Wire Code, 5' Length

By Hubbell Wiring Device-Kellems
Catalog # [PN1004PA005](#)

Signal And Control, Linkosity, Cordset, Male, Single Ended 90
Degree, 4-Wire, 10A 600V AC, PA Wire Code, 5' Length

Features

- Linkosity
- Cordset
- Male
- Single Ended 90 Degree

Application

Quick Connect/Disconnect Signal and Control

General

Catalog Number	PN1004PA005
Color	Gray
EU RoHS Indicator	No
Insulation	PVC
Item Type	Male Angled Plug
Jacket	PVC
OEM Brand Name	Hubbell Wiring Device-Kellems
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585192956



Dimensions

Diameter Live Part	.46"
--------------------	------

Conductor Related

Conductor Type	Copper
Number of Conductors	4-Pole

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Installation Manuals - WIRING_PD2038_INSTALLINST](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - Linkosity Wiring System](#)
- [Specifications - PN1004PA005](#)
- [Warranty - Industrial & Commercial Products](#)