



Wiring Device-Kellems

Signal And Control, Linkosity, Cordset, Male, Single Ended 90 Degree, 4-Wire, 10A 600V AC, PA Wire Code, 10' Length

By Hubbell Wiring Device-Kellems
Catalog # [PN1004PA010](#)



Signal And Control, Linkosity, Cordset, Male, Single Ended 90 Degree, 4-Wire, 10A 600V AC, PA Wire Code, 10' Length

Application

Quick Connect/Disconnect Signal and Control

General

Color	Gray
EU RoHS Indicator	No
Insulation	PVC
Item Type	Male Angled Plug
Jacket	PVC
OEM Brand Name	Hubbell Wiring Device-Kellems
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585192963

Dimensions

Diameter Live Part	.46"
--------------------	------

Conductor Related

Conductor Type	Copper
Number Of Conductors	4-Pole

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Installation Manuals - WIRING_PD2038_INSTALLINST](#)
- [Literature - WIRING_WLFVM034](#)
- [Literature - Linkosity Wiring System](#)
- [Literature - Pulp & Paper Solutions](#)
- [Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.