

Linkosity, Male Right Angle Cable, 4-Wire, 10A, 5' Cable.

By Hubbell Wiring Device-Kellems Catalog # PN1004PB005

Linkosity, Male Right Angle Cable, 4-Wire, 10A, 5' Cable.

Application

Quick Connect/Disconnect Signal and Control

General

Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	Single Ended Cable with Male 90 Degree Connector
OEM Brand Name	Hubbell Wiring Device- Kellems
Plug Type	Linkosity
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585128184
Dimensions	
Outside Diameter	0.75



Electrical Ratings

Amperage Rating Current / Amperage Rating Current Rating Voltage Rating	10 A 10 A 10 A 600V kV	
Conductor Related		
Conductor Size Conductor Type Number Of Conductors Strands	#12 AWG Copper 4-Pole Multi	
Logistics		
Carton Quantity	10	

Product Assets

Installation Manuals - WIRING_PD2038_INSTALLINST Literature - WIRING_WLFVM034 Literature - Linkosity Wiring System Literature - Pulp & Paper Solutions Warranty - Industrial & Commercial Products