



Wiring Device-Kellems

Signal And Control, Linkosity, Cordset, Male, Single Ended 90 Degree, 5-Wire, 20A 600V AC, PA Wire Code, 10' Length



By Hubbell Wiring Device-Kellems
Catalog # [PN2005PA010](#)

Signal And Control, Linkosity, Cordset, Male, Single Ended 90 Degree, 5-Wire, 20A 600V AC, PA Wire Code, 10' Length

Application

Quick Connect/Disconnect Signal and Control

General

Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	Single Ended Cable with Male 90 Degree Connector
OEM Brand Name	Hubbell Wiring Device-Kellems
Plug Type	Linkosity
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585243030

Dimensions

Outside Diameter	0.75
------------------	------

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Current Rating	20 A
Voltage Rating	600V kV

Conductor Related

Conductor Size	#12 AWG
Conductor Type	Copper
Number Of Conductors	5-Pole
Strands	Multi

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Installation Manuals - WIRING_PD2033_INSTALLINST](#)
- [Literature - WIRING_WLFVM034](#)
- [Literature - Linkosity Wiring System](#)
- [Literature - Pulp & Paper Solutions](#)
- [Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.