

Linkosity, 20A Single, Male, Right Angle Cable, 15'

By Hubbell Wiring Device-Kellems
Catalog # [PN2304PB015](#)

Linkosity, 20A Single, Male, Right Angle Cable, 15'



General

Application	Quick Connect/Disconnect Signal and Control
Catalog Number	PN2304PB015
Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	Single Ended Cable with Male 90 Degree Connector
OEM Brand Name	Hubbell Wiring Device-Kellems
Plug Type	Linkosity
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585116969

Dimensions

Outside Diameter	0.75
------------------	------

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Current Rating	20 A
Voltage Rating	600V kV

Conductor Related

Conductor Size	#12 AWG
Conductor Type	Copper
Number of Conductors	4-Pole
Strands	Multi

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - PN2304PB015 AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1996_INSTALLINST](#)
[Literature - Pulp & Paper Solutions](#)
[Literature - Linkosity Wiring System](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Sales Drawings - WDK_PN2304PB015_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand