



Linkosity, 30A Male, Right Angle Cable, 10'

By Hubbell Wiring Device-Kellems
Catalog # [PN3004PA010](#)



Linkosity, 30A Male, Right Angle Cable, 10'

Application

Quick Connect/Disconnect Signal and Control

General

Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	Single Ended Cable with Male 90 Degree Connector
OEM Brand Name	Hubbell Wiring Device-Kellems
Plug Type	Linkosity
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585116983

Dimensions

Outside Diameter	0.75
------------------	------

Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A
Current Rating	30 A
Voltage Rating	600V kV

Conductor Related

Conductor Size	#10 AWG
Conductor Type	Copper
Number Of Conductors	4-Pole
Strands	Multi

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Engineering Drawing - PN3004PA010 AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2034_INSTALLINST](#)
[Literature - WIRING_WLFVM034](#)
[Literature - Linkosity Wiring System](#)
[Literature - Pulp & Paper Solutions](#)
[Sales Drawings - WDK_PN3004PA010_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-PN3004PA010-SPEC-EN | REV 5/2023