

Linkosity, Double Ended Female Right Angle Cable, 4-Wire, 10A, 10' Cable.

By Hubbell Wiring Device-Kellems

Catalog # [PQ2304PB010](#)



Linkosity, Double Ended Female Right Angle Cable, 4-Wire, 10A, 10' Cable.

General

| | |
|--------------------|---|
| Application | Quick Connect/Disconnect Signal and Control |
| Catalog Number | PQ2304PB010 |
| Color | Gray |
| Construction | Fabricated |
| EU RoHS Indicator | Yes |
| Insulation | PVC |
| Item Type | Double Ended Cable with Female 90 Degree Connector |
| OEM Brand Name | Hubbell Wiring Device-Kellems |
| Plug Type | Linkosity |
| Temperature Rating | -20 Deg C to 105 Deg C |
| UPC | 783585128214 |

Dimensions

| | |
|------------------|------|
| Outside Diameter | 0.75 |
|------------------|------|

Electrical Ratings

| | |
|---------------------------|---------|
| Amperage Rating | 20 A |
| Current / Amperage Rating | 20 A |
| Current Rating | 20 A |
| Voltage Rating | 600V kV |

Conductor Related

| | |
|----------------------|--------------------------|
| Conductor Size | #12 AWG, #10 AWG Neutral |
| Conductor Type | Copper |
| Number of Conductors | 4-Pole |
| Strands | Multi |

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Installation Manuals - WIRING_PD1996_INSTALLINST](#)
[Literature - Pulp & Paper Solutions](#)
[Literature - Linkosity Wiring System](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Warranty - Industrial & Commercial Products](#)

