



Wiring Device-Kellems

# Signal And Control, Linkosity, Cordset, Female, Double Ended, 90 Degree, 4-Wire, 10A 600V AC, PA Wire Code, 15' Length



By Hubbell Wiring Device-Kellems  
Catalog # [PQ3004PA015](#)

Signal And Control, Linkosity, Cordset, Female, Double Ended, 90 Degree, 4-Wire, 10A 600V AC, PA Wire Code, 15' Length

### Application

Quick Connect/Disconnect Signal and Control

### General

Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	Double Ended Cable with Female 90 Degree Connector
OEM Brand Name	Hubbell Wiring Device-Kellems
Plug Type	Linkosity
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585128047

### Dimensions

Outside Diameter	0.75
------------------	------

### Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A
Current Rating	30 A
Voltage Rating	600V kV

### Conductor Related

Conductor Size	#10 AWG
Conductor Type	Copper
Number Of Conductors	4-Pole
Strands	Multi

### Logistics

Carton Quantity	5
-----------------	---

### Product Assets

- [Installation Manuals - WIRING\\_PD2034\\_INSTALLINST](#)
- [Literature - WIRING\\_WLFVM034](#)
- [Literature - Linkosity Wiring System](#)
- [Literature - Pulp & Paper Solutions](#)
- [Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
WDK-PQ3004PA015-SPEC-EN | REV 5/2023