

Signal And Control, Linkosity,
Cordset, Double Ended Cable, 2) 90
Degree Fittings, 4-Wire, 10A 600V
AC, PE Wire Code, 50' Length

By Hubbell Wiring Device-Kellems
Catalog # [PS1012PE050](#)

Signal And Control, Linkosity, Cordset, Double Ended Cable, 2)
90 Degree Fittings, 4-Wire, 10A 600V AC, PE Wire Code, 50'
Length

Features

- Linkosity
- Cordset
- Double Ended Cable
- 2) 90 Degree Fittings

Application

Quick Connect/Disconnect Signal and Control

General

Catalog Number	PS1012PE050
Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	Double Ended Cable with 2) 90 Degree Connectors
OEM Brand Name	Hubbell Wiring Device-Kellems
Plug Type	Linkosity
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585131092

Dimensions

Outside Diameter	0.89
------------------	------



Electrical Ratings

Amperage Rating	7 A
Current / Amperage Rating	7 A
Current Rating	7 A
Voltage Rating	600V kV

Conductor Related

Conductor Size	#14 AWG
Conductor Type	Copper
Number of Conductors	12-Pole
Strands	Multi

Logistics

Carton Quantity	5
-----------------	---

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Installation Manuals - WIRING_PD2038_INSTALLINST](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - Linkosity Wiring System](#)
- [Specifications - PS1012PE050](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Linkosity®](#)