

Linkosity, 20A Single, Male Female Right Angle Cable, 10'

By Hubbell Wiring Device-Kellems
Catalog # [PS2304PB010](#)

Linkosity, 20A Single, Male Female Right Angle Cable, 10'

Features

- Linkosity
- 20A Single
- Male Female Right Angle Cable
- 10'

Application

Quick Connect/Disconnect Signal and Control

General

| | |
|--------------------|---|
| Catalog Number | PS2304PB010 |
| Color | Gray |
| Construction | Fabricated |
| EU RoHS Indicator | Yes |
| Insulation | PVC |
| Item Type | Double Ended Cable with 2) 90 Degree Connectors |
| OEM Brand Name | Hubbell Wiring Device-Kellems |
| Plug Type | Linkosity |
| Temperature Rating | -20 Deg C to 105 Deg C |
| UPC | 783585116839 |

Dimensions

| | |
|------------------|------|
| Outside Diameter | 0.75 |
|------------------|------|

Electrical Ratings

| | |
|---------------------------|---------|
| Amperage Rating | 20 A |
| Current / Amperage Rating | 20 A |
| Current Rating | 20 A |
| Voltage Rating | 600V kV |

Conductor Related

| | |
|----------------------|--------------------------|
| Conductor Size | #12 AWG, #10 AWG Neutral |
| Conductor Type | Copper |
| Number of Conductors | 4-Pole |
| Strands | Multi |

Logistics

| | |
|-----------------|---|
| Carton Quantity | 5 |
|-----------------|---|

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - PS2304PB010 AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD1996_INSTALLINST](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - Linkosity Wiring System](#)
- [Sales Drawings - WDK_PS2304PB010_DRAWING_PDF](#)
- [Specifications - PS2304PB010](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Linkosity®](#)

