



## Linkosity, 20A Single, Male Female Right Angle Cable, 15'

By Hubbell Wiring Device-Kellems  
Catalog # [PS2304PB015](#)



Linkosity, 20A Single, Male Female Right Angle Cable, 15'

### Application

Quick Connect/Disconnect Signal and Control

### General

Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	Double Ended Cable with 2) 90 Degree Connectors
OEM Brand Name	Hubbell Wiring Device-Kellems
Plug Type	Linkosity
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585116846

### Dimensions

Outside Diameter	0.75
------------------	------

### Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Current Rating	20 A
Voltage Rating	600V kV

### Conductor Related

Conductor Size	#12 AWG, #10 AWG Neutral
Conductor Type	Copper
Number Of Conductors	4-Pole
Strands	Multi

### Logistics

Carton Quantity	5
-----------------	---

### Product Assets

[Engineering Drawing - PS2304PB015 AutoCAD Drawing](#)  
[Installation Manuals - WIRING\\_PD1996\\_INSTALLINST](#)  
[Literature - WIRING\\_WLFVM034](#)  
[Literature - Linkosity Wiring System](#)  
[Literature - Pulp & Paper Solutions](#)  
[Sales Drawings - WDK\\_PS2304PB015\\_DRAWING\\_PDF](#)  
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
WDK-PS2304PB015-SPEC-EN | REV 5/2023