



Wiring Device-Kellems

Signal And Control, Linkosity, Cordset, Double Ended Cable, 2) 90 Degree Fittings, 4-Wire, 30A 600V AC, PB Wire Code, 10' Length



By Hubbell Wiring Device-Kellems
Catalog # [PS3004PB010](#)

Signal And Control, Linkosity, Cordset, Double Ended Cable, 2) 90 Degree Fittings, 4-Wire, 30A 600V AC, PB Wire Code, 10' Length

Application

Quick Connect/Disconnect Signal and Control

General

Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	Double Ended Cable with 2) 90 Degree Connectors
OEM Brand Name	Hubbell Wiring Device-Kellems
Plug Type	Linkosity
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585128054

Dimensions

Outside Diameter	0.75
------------------	------

Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A
Current Rating	30 A
Voltage Rating	600V kV

Conductor Related

Conductor Size	#10 AWG
Conductor Type	Copper
Number Of Conductors	4-Pole
Strands	Multi

Logistics

Carton Quantity	5
-----------------	---

Product Assets

- [Installation Manuals - WIRING_PD2034_INSTALLINST](#)
- [Literature - WIRING_WLFVM034](#)
- [Literature - Linkosity Wiring System](#)
- [Literature - Pulp & Paper Solutions](#)
- [Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-PS3004PB010-SPEC-EN | REV 5/2023