



Copper Solutions, Patch Cord, Cat5E, PS5E, Shielded, Gray, 20' Length

By Hubbell Wiring Device-Kellems
Catalog # [PS5E20GY](#)



Copper Solutions, Patch Cord, Cat5E, PS5E, Shielded, Gray, 20' Length

Features

- Third Party Verified Category 5E Component
- Plug Optimized for High Density Switch Ports
- Qualified to 150% of 802.3bt PoE Current Level
- 100% Performance Tested

Application

Category 5e

General

Attenuation	.1dB
Boot Type	PVC
Color	Gray
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	RJ45
Temperature Rating	Per TIA
UPC	662620288734

Dimensions

Outside Diameter	0.218
------------------	-------

Electrical Ratings

Voltage Rating	300V AC kV
----------------	------------

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number Of Conductors	8-Conductor
Wire Size	#24 AWG

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Warranty - Industrial & Commercial Products](#)

Related Products

- [PS5E07GY - Patch Cord, Cat5e/PS5e, Shielded, Gray, 7'](#)
- [PS5E05GY - Copper Solutions, Patch Cord, Cat5E, PS5E, Shielded, Gray, 5' Length](#)
- [PS5E01GY - Copper Products, Patch Cord, Cat5E, PS5E, Shielded, Gray, 1' Length](#)
- [PS5E15GY - Copper Solutions, Patch Cord, Cat5E, PS5E, Shielded, Gray, 15' Length](#)
- [PS5E10GY - Patch Cord, Cat5e/PS5e, Shielded, Gray, 10'](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-PS5E20GY-SPEC-EN | REV 5/2023