



2" Tough Floor Fitting

By Hubbell Wiring Device-Kellems
Catalog # [PT27A](#)

Fire-Rated Poke-Through Pedestal Series, 2" Tough Floor Fitting



Application

Through Floor Fitting

General

EU RoHS Indicator	No
Item Type	Through Floor Fitting
Material	Composite
Material - Mounting Hardware	N/A
OEM Brand Name	Hubbell Wiring Device-Kellems
Performance	<ul style="list-style-type: none">• Electrical - Power Wiring Capacity - Up to ten #12 AWG type THHN wires, or Up to six #12 AWG and two #10 AWG type THHN wires• Electrical - Voice/Data Wiring Capacity - Up to two 25 pair tel./data cables (100 #22 AWG tel./data conductors), or Up to two IBM Type 2 data cables• Mechanical - Max. Cu Cross Section - 1/2" Power EMT .0461 sq. in., 3/4" Low Voltage EMT .0500 sq. in.• Mechanical - UL Spacing Restrictions - Min. of 2 ft. O.C. and not more than one unit per each 65 sq. ft. of floor area in each span
Style	Through-Floor Fittings
UPC	783585076157

Dimensions

Display Size Standard Sized Product

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Fire Resistance - R8429• Outlet Box- E31999
----------------------	--

Product Assets

[Catalog Page - Wiring Q-34 Catalog page](#)
[Catalogs - Wiring Full Catalog](#)
[Engineering Drawing - PT27A AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1901_INSTALLINST](#)
[Sales Drawings - WDK_PT27A_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)

Related Products

[FR480BKA - Pedestal, 4-Gang, Black](#)
[FR280GYA - Pedestal, 2-Gang, Gray](#)
[FR480GYA - Pedestal, 4-Gang, Gray](#)
[FR280ALA - Pedestal, 2-Gang, Almond](#)
[FR280BKA - Pedestal, 2-Gang, Black](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-PT27A-SPEC-EN | REV 5/2023